

---

## [E-Light Beauty Equipment](#)

### **E-Light Beauty Equipment**

Welcome to Noble Laser! Here we will show you our E-light beauty equipment.

By taking advantage of skin's selective absorption on light, the E-light beauty machine generates light at different wavelengths to induce the pyrolysis of lesion tissues in epidermis and dermis, thus achieving beauty effect. As the light energy and RF energy in E light system can be independently controlled, the E-light beauty equipment can be controlled to generate relatively low light energy and high RF energy, so as to reduce the risk of epidermis burning during wrinkle removal, speckle eliminating and skin rejuvenation processes.

Noble E-light beauty equipment falls into Eos Super and Eos Portable series which are subdivided into 6 models. Eos Super series vertical E light beauty machines are equipped with 8.4 inch display screen and the power supply is 800W. While Eos Portable series are portable machines with 5.7 inch LCD, and the power supply is 400W. They are all CE certified, and widely used in professional beauty hospitals, clinics, spas, salons, laser beauty institutions and beauty salons, etc.

#### **Applications**

E-light beauty equipment can be used to remove color spot, unwanted body hair, especially fine hair and treat telangiectasis. It's also used to eliminate wrinkles, whiten and soften skin, and improve the sensitive skin effectively.

#### **Advantages**

1. With huge water tank and semiconductor cooling system, our E-light beauty equipment can work 24 hours continuously.
2. Noble E light beauty machinery has three kinds of handpiece for you to choose, integrated high power handpiece, handpiece with five filters, portable handpiece with 4 adjustable gem heads. Integrated high power handpiece with output energy 20 percent higher than the others is our patented product.
3. Noble E-light beauty machine comes with 8.4 or 10.4 inch LCD real color touch screen and it has five different wavelength filters for your option.
4. Using both IPL and bipolar RF technologies, our beauty equipment can achieve deeper skin penetration.
5. Designed with wheels, this beauty instrument is convenient for transportation.
6. With expert control system, the beauty machine is able to adjust the parameters according to the skin color of customers automatically.
7. The exterior cover of this equipment is anticorrosive due to our adoption of the best painting system. The color of crusts can be chosen according to customer's requirement.
8. E-light beauty equipment is packed with aluminium plane cases, most suitable for long distance sea transportation.

#### **Technical parameters of E-light beauty equipment**

Model: Eos Super-A, Eos Super-B, Eos Super-C, Eos Portable-A, Eos Portable-B, Eos Portable-C

Lamp-house	Super intense pulsed light
Range of Spectrum	480-1200nm: remove acne
	530 -1200nm: speckle treatment
	560 -1200nm: skin rejuvenator
	590-1200nm: remove vessel
	640 -1200nm: remove unwanted hair
	690-1200nm: remove unwanted hair
RF Frequency	6MHZ
RF Maximum Out	Maximum:100J/CM3
Density of Energy	50J/cm2
Size of Spot	8*40mm2/16*40 mm2
Amount of Pulse	2~6, adjustable
Interval of Pulse	1~99ms, adjustable
Sub-pulse Width	0.1~9.9ms, adjustable
Cycle	1~4s, adjustable
Cooling Way	semi-conductor cooling
Screen	8.4/10.4 inch color touch screen
Power Supply	220V ±10% 50Hz, 110V ±10% 60Hz

In addition to E light beauty equipment, we also provide IPL skin rejuvenation equipment, laser tattoo removal machine, and body slimming machine, etc. We provide all our beauty apparatus with one year quality guarantee and lifelong maintenance services. When as many as 50 sets of beauty machines are purchased, we will offer a set of accessories, free of charge. These accessories worth 1/2 of the beauty machine itself. Usually, we can deliver goods in three work days. If you want to know more about our beauty equipment, please go to related product pages or contact us directly.

## **FEED BACK FORM**

---

E-mail:

Message:

Product Name:

Your Name:

Company:

FAX / TEL:

MSN/SKYPE

Address: